

Pressure
Temperature
Level
Calibration

Instrumentation for **high-pressure** applications



WIKAI

Part of your business

Instrumentation for high-pressure applications

Specific materials with high-yield characteristics and special manufacturing processes such as vacuum soldering ensure the high quality of these products, individually matched to your requirements. The process of producing LDPE (Low Density Polyethylene) or EVA (Ethylene Vinyl Acetate) is made at pressures of approx. 3,000 bar, where the temperature curve in the high-pressure tubular and autoclave reactors is an important process variable.


Temperature measurement

High-pressure thermocouple
TC90




Each high-pressure thermocouple is designed and manufactured in accordance with customer requirements. Through pressure testing up to 6,000 bar, we ensure the high demands on safety and reliability.

High-pressure multipoint
for applications such as
autoclave reactors
TC95



Temperature transmitter
T32



The 4 ... 20 mA/HART® temperature transmitter T32 has a large installed base in petrochemical plants worldwide. Additionally, an ultra-fast version, T32.1R, has been developed especially for LDPE/EVA applications.

- Fast response time
- Universally programmable
- Global approvals for hazardous areas

Available tests and certificates

- 2.2 test report
- 3.1 inspection certificate
- 3.1 material certificate
- 3.2 material certificate
- DKD/DAkkS calibration certificate
- Climatic tests
- Shock and vibration tests
- Response time tests
- Pressure cycle tests
- Pressure strength and burst pressure tests
- IP protection tests
- EMC tests
- Dye penetrant testing
- X-ray testing of components

Pressure measurement

The model IS-3 pressure sensor is available with measuring ranges up to 6,000 bar. A wide range of process connections are available.

- Fast response time
- High shock and vibration resistance
- Global approvals for hazardous areas



Pressure sensor
IS-3

Calibration up to 10,000 bar



Precision digital
pressure gauge
CPG1500

Comparison pump
CPP7000-X

To meet maintenance requirements, a hydraulic comparison pump can be used to generate high pressures and a digital gauge can be used as a reference. Thus high-pressure intrinsically safe pressure transmitters can be calibrated easily in a workshop.


The digital pressure gauge can be utilised for on-site calibration, comparison measurements or for data logging up to 10,000 bar.

Level measurement

Magnetic bypass level indicators allow for clear local indication as well as remote transmission of fluid levels. Each unit is precisely engineered to the fluidic properties of the process media.

Typical applications include level measurement of lubricating oil.

Bypass level
indicator





WIKA worldwide

Europe

Austria
WIKA Messgerätevertrieb
Ursula Wiegand GmbH & Co. KG
info@wika.at
www.wika.at

Belarus
WIKA Belrus
info@wika.by
www.wika.by

Benelux
WIKA Benelux
Industrial estate De Berk
info@wika.nl
www.wika.nl

Bulgaria
WIKA Bulgaria EOOD
info@wika.bg
www.wika.bg

Croatia
WIKA Croatia d.o.o.
info@wika.hr
www.wika.hr

Denmark
WIKA Denmark A/S
info@wika.as
www.wika.as

Finland
WIKA Finland Oy
info@wika.fi
www.wika.fi

France
WIKA Instruments s.a.r.l.
Immeuble Le Trident
info@wika.fr
www.wika.fr

Germany
WIKA Alexander Wiegand SE & Co. KG
info@wika.de
www.wika.de

Italy
WIKA Italia S.r.l. & C. S.a.s.
info@wika.it
www.wika.it

Poland
WIKA Polska spółka z ograniczoną
odpowiedzialnością sp. k.
info@wikapolska.pl
www.wikapolska.pl

Romania
WIKA Instruments Romania S.R.L.
info@wika.ro
www.wika.ro

Russia
AO WIKA MERA
info@wika.ru
www.wika.ru

Serbia
WIKA Merna Tehnika d.o.o.
info@wika.rs
www.wika.rs

Spain
Instrumentos WIKA S.A.U.
info@wika.es
www.wika.es

Switzerland
WIKA Schweiz AG
info@wika.ch
www.wika.ch

Turkey
WIKA Instruments
Endüstriyel Ölçüm Cihazları Tic. Ltd. Şti.
info@wika.com.tr
www.wika.com.tr

Ukraine
TOV WIKA Prylad
info@wika.ua
www.wika.ua

United Kingdom
WIKA Instruments Ltd
info@wika.co.uk
www.wika.co.uk

North America

Canada
WIKA Instruments Ltd.
Head Office
info@wika.ca
www.wika.ca

USA
WIKA Instrument, LP
info@wika.com
www.wika.com

Latin America

Argentina
WIKA Argentina S.A.
info@wika.com.ar
www.wika.com.ar

Brazil
WIKA do Brasil Ind. e Com. Ltda.
vendas@wika.com.br
www.wika.com.br

Chile
WIKA Chile S.p.A.
info@wika.cl
www.wika.cl

Colombia
Instrumentos WIKA Colombia S.A.S.
info@wika.co
www.wika.co

Mexico
Instrumentos WIKA Mexico
S.A. de C.V.
ventas@wika.com
www.wika.mx

Asia

China
WIKA Instrumentation Suzhou Co., Ltd.
info@wika.cn
www.wika.com.cn

India
WIKA Instruments India Pvt. Ltd.
sales@wika.co.in
www.wika.co.in

Iran
WIKA Instrumentation Pars Kish (KFZ)
Ltd.
info@wika.ir
www.wika.ir

Japan
WIKA Japan K. K.
info@wika.co.jp
www.wika.co.jp

Kazakhstan
TOO WIKA Kazakhstan
info@wika.kz
www.wika.kz

Korea
WIKA Korea Ltd.
info@wika.co.kr
www.wika.co.kr

Malaysia
WIKA Instrumentation (M) Sdn. Bhd.
info@wika.my
www.wika.my

Philippines
WIKA Instruments Philippines Inc.
info@wika.ph
www.wika.ph

Singapore
WIKA Instrumentation Pte. Ltd.
info@wika.sg
www.wika.sg

Taiwan
WIKA Instrumentation Taiwan Ltd.
info@wika.tw
www.wika.tw

Thailand
WIKA Instrumentation Corporation
(Thailand) Co., Ltd.
info@wika.co.th
www.wika.co.th

Africa / Middle East

Egypt
WIKA Near East Ltd.
info@wika.com.eg
www.wika.com.eg

Namibia
WIKA Instruments Namibia Pty Ltd.
info@wika.com.na
www.wika.com.na

South Africa
WIKA Instruments Pty. Ltd.
sales@wika.co.za
www.wika.co.za

United Arab Emirates
WIKA Middle East FZE
info@wika.ae
www.wika.ae

Australia

Australia
WIKA Australia Pty. Ltd.
sales@wika.com.au
www.wika.com.au

New Zealand
WIKA Instruments Limited
info@wika.co.nz
www.wika.co.nz

Pictures from:
fotolia.de and shutterstock.com

WIKA Alexander Wiegand SE & Co. KG
Alexander-Wiegand-Straße 30 · 63911 Klingenberg · Germany
Tel. +49 9372 132-0 · Fax +49 9372 132-406
info@wika.de · www.wika.de

14225593 03/2018 EN

